Job Traveler

Due Date: 11/08/2023

Job Number: 231755-05

Sold EDGEN MURRAY CORPORATION

To: 18444 HIGHLAND ROAD

P.O. BOX 84160

BATON ROUGE, LA 70884-4160

United States

Ship

To: , LA

United States

Order No: 231755

Dated: 09/12/202:

Quote No: 20723

Customer: EDGEN119955

PO Num: RMS-300904

Ship Via: TIFFANY.BAKER@EDGENMURR

Priority: 3 - STANDARD

Part Number: *3CR2416Y

Product Code: CONCENTRIC REDUCER

Description: CR 24X16 .562 X .500-

Master Job No:

WPHY65

TAG: PUR-5020-2010483

LINE 11, EN-341

PUR-5020-2010483

LINE 11, EN-342

ES-PF1.14

Total Qty Open: 2 EA

Qty Posted: 0 EA Qty To Make: 2

Start Date: 09/26/2023 Contact: CLAIRE BLAY Phone: 2,257,569,868

Fax:

Job Notes

BCLD B10608-1

CUT (2) @ 21.5" EACH FROM 46" PIECE; FULL PIECE ALLOCATED

Routing

Routed By:

Work Cntr / Vendor Operation

Description

Setup **Time** Cycle Time Total **Time**

Pieces Per Hour --- Scheduled ---

End

Quantity 2

Run Quantity

10

Dept

Step No

FORGE 10 CYLINDER CUT Cylinder Cut Cylinder Cut 09/26/2023 09/26/2023

Start

2





20

FORGE 4 HAMMER Large Hammer Hammer

10/09/2023 10/09/2023








Job Number: 231755-05

Report Generated: 09/14/2023 8:51:04 AM





100 SHIPPING SHIPPING Shipping

02/18/2025 02/18/2025





Time per Piece (HR): Total Time for Job (HR): 0.00 0.00 0.00 0.00 0.00 0.00 0.00

Job Number: 231755-05

Report Generated: 09/14/2023 8:51:04 AM

2

Materials List

g							Quantity:	2
	******************	Quantity		***********			Sub-	
	Needed	On Hand	<u>Posted</u>	<u>Short</u>	<u>Unit</u>	Description	Assy	Vendor
4	6.00000	317.00000	46.00000	0.00000	EA	0PI247552-W	NO	SFI
						PI0 2475-Y52 W		

PI0 24-.75-Y52 W Quantities from Bins/Lot Number: BCLD (46.0)

Job Number: 231755-05

Report Generated: 09/14/2023 8:51:04 AM

Marking Information:



FLEET-LINE MADE IN USA STEEL FORGINGS

BCLD 24X16 .562X.500 WPHY65 231755-05

DOCUMENT PACKAGE

Fitting Description		
SFI Serial Number	231755-05	
Spectra Serial Number	PO SEE FRO	NT SHEET
-ME inspection repor	ŧ	
MTR's		
Reader Sheet for Ra	diography	
Inspection sheet wi	th actual dimensions	
Heat Treat charts		
Furnace Uniformity	& Quarterly Recorder Ca	alibration records

DIMENSIONAL INSPECTION SHEET FOR TEE

Does stamping match traveler?	
What is actual run bevel thickness?	
What is actual outlet bevel thickness?	
What is the length of the tee?	
What is actual ID of run at bevel? (Check two places)	
What is actual ID of outlet? (Check two places)	
What is M dimension?	
Is outlet centered?	
Are all three bevels 30°+5°/ -0°?	
SFI serial number stamped on it?	
Spectra serial number stamped on it?	
Have all areas needing cosmetic grinding been marked?	
Grind weld seam inside and outside flush for minimum 2" from ends.	

FORM BY EXTRUSION PER CARD:				
PRE CUT ENDS				
IF ORDER SIZE IS LARGER THAN FURNACE LOAD, SERIALIZE UNDER CUTTER STAMP PRIOR TO HEAT TREAT				
HEAT TREATMENT PER QCP 8.1 REV.1: (WITH TEST MAT'L B)				
HEAT TREAT HR @ 1650°F WATER QUENCH FURNACE LOAD #				
TEMPER 3/4 HR @ 1300 °F - AIR COOL - FURNACE LOAD#				
IF QUENCH AND TEMPERED, RECORD THE FOLLOWING				
TIME FROM FURNACE TO QUENCH TANK				
TEMPERATURE OF QUENCH TANK				
SHOTBLAST TO NEAR WHITE FINISH				
100% RADIOGRAPH WELD SEAM PER SPEC. XL-RT-100 (LATEST REVISION)				
DO NOT MACHINE UNTIL TESTING COMPLETE				
MACHINE PER MSS-SP75-19 EXCEPT 14° MIN., 18° MAX INTERNAL TAPER				
16 in. (SMALL) END-STRAIGHT BORE I.D. TO 14.500 ± 1/16 (FACE, TAPER BORE, AND BEVEL)				
ME ALL WELD BEVELS PER SPEC. XL-MT-100 (LATEST REVISION) AND PF1.1 PARA 7A10 (5/28/18) ATTACH REPORTS				
STAMP PER MSS-SP75-19 ON O.D. A MINIMUM OF 2" FROM BEVEL & WELD SEAM				
SFI SERIAL NUMBER 231755-05				
SPECTRA SERIAL NUMBER PO SEE FRONT SHEET				
HARDNESS TEST EACH PIECE (235 BHN MAX):				
PAINT EXTERIOR ONLY - AFTER INSPECTION				
PAINT RED FLOURESCENT STRIPE DOWN LENGTH OF FITTING IF CE> .42 CE=				
END PROTECT/PALLETIZE				
CUSTOMER INSPECTION MAY BE REQUIRED				
MPS & ITP FOR PF1.9 REV. 0 IS APPROVED 3/1/12 PER REX LITTRELL, SPECTRA ENERGY				

Base and weld charpies min 20/15
CE .45 or less
ME bevels
Base hardness
QT can only be used for Y52 and up
S:\PUBLIC\TAVELER\Spectra PF1.14\PF1.14 Travelers.XLSX